











Тип ОА	Радиус кривизны ОА, мм	Диаметр ОА, мм	Угол между ушками, °	Высота ушек, мм	Вариант исполнения ушек	Активность, МБк
	Sr.01-A 12 13 14	12-21 12-23 12-24	-	-	-	до 300
	Sr.01-B 12 13 14	12-21 12-23 12-24	-	-	-	до 300
	Sr.01-C 12 13 14	12-21 12-23 12-24	-	-	-	до 300
	Sr.02-A 12 13 14	12-21 12-23 12-24	-	-	-	до 300
	Sr.02-B 12 13 14	12-21 12-23 12-24	-	-	-	до 300
	Sr.03 Sr.04 Sr.05 Sr.07 12 13 14	12-21 12-23 12-24	60° 50° 45° 50°	3,3 5,8 3,3 5,0		30-60
	Sr.06-A 12 13 14	12-21 12-23 12-24	45° 45°	6,3 6,3		30-60
	Sr.06-B 12 13 14	12-21 12-23 12-24	175° 175°	6,3 6,3		30-60
	Sr.08 12-14	-	-	-	-	30-60
	Sr.09 12 13 14	12-21 12-23 12-24	-	-	-	30-60

Примечания:

1. Sr. – офтальмоаппликаторы с изотопом стронция – 90 (всего 29 разновидностей).